

Metal Parts, current up to 350A

| Picture | Product serie | Description | Material | Rated current(A) | Nut specification | Torsion | Connection direction |
|---------|---------------|----------------------|------------|------------------|-------------------|----------|----------------------|
| | K13-00A(H) | Extraction nut | Orichalcum | 15 | M4 | 1.2 N·m | |
| | K14-00A(H) | Extraction nut | Orichalcum | 15 | M3.5 | 0.8 N·m | |
| | K92-01A(H) | One-piece formed nut | Orichalcum | 25 | M4 | 2.0 N·m | |
| | K93-01A(H) | One-piece formed nut | Orichalcum | 25 | M4 | 2.0 N·m | |
| | K15-00A(H) | Extraction nut | Orichalcum | 26 | M3.5 | 0.8 N·m | |
| | K48-00A(H) | Riveted nut | Orichalcum | 30 | M4 | 1.6 N·m | |
| | K46-00A(H) | Extraction nut | Orichalcum | 38 | M3 | 0.5 N·m | |
| | K31-00A(H) | Extraction nut | Orichalcum | 40 | M4 | 1.2 N·m | |
| | K99-00A(H) | Extraction nut | Orichalcum | 40 | M4 | 1.2 N·m | |
| | K128-00A(H) | One-piece formed nut | Orichalcum | 40 | M4 | 1.2 N·m | |
| | K45-00A(H) | Extraction nut | Orichalcum | 50 | M4 | 1.2 N·m | |
| | K50-00A(H) | Extraction nut | Red copper | 50 | M4 | 1.2 N·m | |
| | K91-00A(H) | Extraction nut | Red copper | 50 | M4 | 1.32 N·m | |
| | K145-00A(H) | One-piece formed nut | Orichalcum | 50 | M4 | 1.5 N·m | |
| | K40-00A(H) | One-piece formed nut | Orichalcum | 60 | M4 | 1.8 N·m | |

Metal Parts, current up to 350A

| Picture | Product serie | Description | Material | Rated current(A) | Nut specification | Torsion | Connection direction |
|---------|---------------|----------------------|------------|------------------|-------------------|----------|----------------------|
| | K94-01A(H) | Riveted nut | Orichalcum | 60 | M3 | 1.0 N·m | |
| | K115-00A(H) | Riveted nut | Orichalcum | 63 | M4 | 1.8 N·m | |
| | K34-00A(H) | Extraction nut | Orichalcum | 65 | M5 | 2.0 N·m | |
| | K68-00A(H) | Riveted nut | Orichalcum | 80 | M5 | 2.4 N·m | |
| | K116-00A(H) | Riveted nut | Red copper | 85 | M5 | 2.0 N·m | |
| | K51-00A(H) | Extraction nut | Orichalcum | 92 | M5 | 2.0 N·m | |
| | K146-00A(H) | Riveted nut | Red copper | 110 | M6 | 2.75 N·m | |
| | K147-00A(H) | Riveted nut | Red copper | 110 | M6 | 2.75 N·m | |
| | K36-00A(H) | Extraction nut | Red copper | 115 | M6 | 1.8 N·m | |
| | K44-00A(H) | Riveted nut | Red copper | 115 | M5 | 2.0 N·m | |
| | K80-00A(H) | Riveted nut | Red copper | 115 | M5 | 3.0 N·m | |
| | K96-00A(H) | Riveted nut | Red copper | 200 | M8 | 3.5 N·m | |
| | K41-00A(H) | Riveted nut | Red copper | 250 | M6 | 1.98 N·m | |
| | K59-00A(H) | One-piece formed nut | Red copper | 269 | M6 | 3.5 N·m | |
| | K136-00A(H) | One-piece formed nut | Red copper | 350 | M6 | 4.5 N·m | |